



INDUSTRIAL & COMMERCIAL TRANSPORTATION SERIES BRIEF

Rugged Single-Pole Power Interconnect Solution

TE Connectivity's DEUTSCH DTSK connectors are easy-to-use, single-pole connectors designed for power applications. They can be used either inline or as a pass-through with an optional mounting flange. These heavy-duty thermoplastic connectors accept size Ø8mm contacts that are rated up to

Featured:

DEUTSCH DTSK CONNECTORS

SPECIFICATIONS

Current Rating:

125 amps using 35mm² wire

Immersion:

IP68 & IP69K

Maximum Voltage:

250VAC/VDC

Operating Temperature:

-55°C to +125°C

Additional Information:

- Product Specification, 108-151027
- Application Specification (Connector System), 114-151028
- Application Specification (Contacts), 114-151039



125 amps. Designed with ease of use and simplicity in mind, DEUTSCH DTSK connectors feature latch-style mating and an integrated secondary lock. Single wire seals and a rear protective cover are designed to prevent dirt, dust and moisture from contaminating connections. For applications that require a rugged and environmentally-sealed power connector, the DEUTSCH DTSK connectors are a reliable solution.

Common Part Numbers

Here are some of the common part numbers for DEUTSCH DTSK connectors and related products.

Description	Part Number
Plug housing, Key A, gray	DTSK06-1-08SA
Plug housing, Key B, black	DTSK06-1-08SB
Plug housing, Key C, brown	DTSK06-1-08SC
Receptacle housing, Key A, gray	DTSK04-1-08PA
Receptacle housing, Key B, black	DTSK04-1-08PB
Receptacle housing, Key C, brown	DTSK04-1-08PC
Pin contact, Ø8mm, 4AWG (25mm ²) wire*	SRK-PC-080-25-601
Pin contact, Ø8mm, 2AWG (32mm ²) wire*	SRK-PC-080-32-601
Pin contact, Ø8mm, 35mm ² wire*	SRK-PC-080-35-601
Socket contact, 8mmØ, 4AWG (25mm ²) wire*	SRK-SC-080-25-601
Socket contact, 8mmØ, 2AWG (32mm ²) wire*	SRK-SC-080-32-601
Socket contact, 8mmØ, 35mm ² wire*	SRK-SC-080-35-601
* CONTACTS ARE CRIMPED USING NFC 20.130 STANDARD CRIMP TOOLS	
Wire seal, 4AWG (25mm ²) wire, 8.17-9.66mm [0.322-0.380"] insulation, Blue	WS-25-001 (2289241-1)
Wire seal, 2AWG (32mm ²) wire, 9.49-10.52mm [0.374-0.414"] insulation, Red	WS-32-001 (2289242-1)
Wire seal, 35mm ² wire, 10.59-11.59mm [.417-.456"] insulation, Green	WS-35-001 (2289243-1)
Mounting flange**	DTSKF-1 (2289235-1)
** REQUIRES SEPARATE AS568-212 O-RING FOR PROPER MOUNTING FIT	
Removal tool	DT-RT1

te.com/ict

DEUTSCH, TE Connectivity, and TE connectivity (logo) are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2018 TE Connectivity Ltd. family of companies All Rights Reserved.

TS-ICT-DEUTSCH-DTSKA4 08/18 Original

SERIES BRIEF

Contact us

Ampèrestrasse 12-14
64625 Bensheim Germany

Tel: +49 (0)6251 133-0

www.te.com

TE Connectivity Germany GmbH