



24 Pin USB 3.2 Type-C

USB4080

- Ⓞ **Cost effective 24 pin SMT USB Type C Horizontal Receptacle.**
- Ⓞ **Full 3.2 Gen 2 Type-C connection.**
- Ⓞ **Designed for Paste in Hole Reflow (PIHR) to maximise production efficiency.**




Vital Stats

Interface	Current Rating
USB C	5 Amps
No. of Contacts	Mating Cycles
24	10,000
USB Specification	Profile Above PCB
3.2 Gen 2	3.16mm

- 1 Horizontally mounted socket
- 2 USB C interface
- 3 24 SMT contacts support USB 3.2 spec
- 4 4 through-hole shell stakes
- 5 Stainless steel shell

Applications

Alarm Systems
Portable Electronics
Security Cameras
Consumer Electronics
Gaming Peripherals



gct.co/connector/usb4080