

MAN & MACHINE

So Cool Keyboard

In-Vehicle Public Safety Grade™
Keyboard



In Demand By Those In Command

Rugged, tough, and built to take whatever the road dishes out — the So Cool is rattle-free, easy to clean, and dependable. The So Cool Keyboard has advanced technology with multi-level backlight and great tactile. This in-vehicle keyboard's exterior is constructed out of a single, solid piece of oil-resistant silicone, with no moving parts that can fail. It easily attaches to all major mounting systems, making it an easy addition to the equipment you presently have in your vehicle.

The So Cool Keyboard is the perfect in-vehicle keyboard for police, fire, and EMS vehicles.

Oil Safe Silicone

Most silicone keyboards have one big weakness: Oil. If your crew has greasy hands or works with oil, gun grease, or anything else, then the So Cool is a solution for you. The So Cool Keyboard will find itself at home in police cars, ambulances, or factories where oil and grease abound.

Multilevel Backlight


Typing at night or in low-level environments does not need to be a hassle. The So Cool Keyboard has a special multilevel backlight with LED bulbs built-in behind every key. Tap the backlight button until you find the perfect level of brightness. From then on, you can tap the button to turn on the backlight at the same level.



Tru-Lock - Lock it, then clean it. TruLock prevents unwanted characters and commands from being nered during cleaning & disinfection procedures.



Sealed Low Profile Design - Easily clean and disinfect between the keys with an EPA-registered wipe.



Private Label - Add a one-color custom logo



Built to Last



Born in the USA

Man & Machine, Inc.

✉ info@mmimd.com 🌐 www.man-machine.com

☎ 301.341.4900



So Cool Keyboard

In-Vehicle Public Safety Grade™ Keyboard

Benefits of a Sealed Keyboard/Mouse

1. Fully Sealed & Seamless
2. Lockable for Workstation Disinfecting
3. Built to Hold Up to Rigors of Harsh Environments & Multiple Users
4. Designed for Use in Dusty Dirty Environments
5. Enhanced Tactile Typing
6. Avoid Velcro™ When Attaching Keyboard to Trays
7. Ergonomic for Staff Safety and Comfort
8. Avoid Anti-Microbial Additives



Features

- TruLock - Lock your keyboard for easy cleaning without disconnecting
- Full-sized keyboard with a low-profile key height for ease of cleaning
- Sealed, Waterproof, & Immersible
- Oil-Safe
- No moving parts, no mechanical failure
- Rugged, durable, dependable design
- Adjustable Backlight
- Cleanable with harsh disinfectants
- TAA Compliant
- 3-year warranty

Specifications

- Material: Silicone Oil-Resistant Rubber, Latex Free
- Size: 12 in x 7.7 in x 1.0 in (305mm x 195mm x 25.5mm)
- Weight: 1.35 lbs (.62 Kg)
- Operating Temperature: range -25 to 85 (degree C)
- Platform: Windows, Mac, Unix, and Linux systems
- Layout: Includes touchpad and 12 Function keys
- Voltage: 5V
- Power Consumption: 200mA
- Current: 300mA (max current when the backlight is on)
- Mount Types: AMPS & VESA mount included
- Protection Rating: IP64
- Compliance: CE, FCC
- Connection: USB

Colors

- Black

Man & Machine, Inc.

✉ info@mmimd.com 🌐 www.man-machine.com

☎ 301.341.4900