


Value-Clamp Structural Blind Rivets



Austin Hardware® is proud to be a Master Distributor of Howmet Fastening Systems' Value-Clamp Structural Blind Rivets. For more information, scan the code to visit us online:



Typical Strength (lbs)

Austin Hardware Value-Clamp Part #	IDG Value-Clamp Part #	Huck MGL X-Ref	A Dia.	Grip Range	Drill No & Holes Sizes	B Head Dia. Nom	C Head Height Max	D Rivet Length Max	Shear	Tensile
Steel/Steel Buttonhead										
VC-MGLP-R6-4	M76807	MGLP-R6-4	3/16"	.062-.272	#11 Drill (.191-.201)	0.402	0.098	0.717	1450	1200
VC-MGLP-R6-7	M76808	MGLP-R6-7	3/16"	.213-.433	#11 Drill (.191-.201)	0.402	0.098	0.965	1450	1200
VC-MGLP-R6-E	M76809	MGLP-R6-E	3/16"	.062-.437	#11 Drill (.191-.201)	0.402	0.098	0.965	1450	1200
VC-MGLP-R6-10	M76896	MGLP-R6-10	3/16"	.455-.665	#11 Drill (.191-.201)	0.402	0.098	0.965	1450	1200
VC-MGLP-R8-6	M76810	MGLP-R8-6	1/4"	.083-.374	F Drill (.261-.272)	0.531	0.122	0.996	2750	2200
VC-MGLP-R8-E	M76812	MGLP-R8-E	1/4"	.083-.622	F Drill (.261-.272)	0.531	0.122	1.402	2750	2200
VC-MGLP-R8-10	M76811	MGLP-R8-10	1/4"	.350-.625	F Drill (.261-.272)	0.531	0.122	1.44	2360	2200
Aluminum/Aluminum Buttonhead										
VC-MGLP-B6-4	M76821	MGLP-B6-4	3/16"	.062-.272	#11 Drill (.191-.201)	0.402	0.098	0.717	700	500
VC-MGLP-B6-7	M76822	MGLP-B6-7	3/16"	.213-.433	#11 Drill (.191-.201)	0.402	0.098	0.965	700	500
VC-MGLP-B6-E	M76823	MGLP-B6-E	3/16"	.062-.437	#11 Drill (.191-.201)	0.402	0.098	0.965	700	500
VC-MGLP-B8-6	M76824	MGLP-B8-6	1/4"	.083-.374	F Drill (.261-.272)	0.531	0.122	0.996	1300	890
VC-MGLP-B8-E	M76826	MGLP-B8-E	1/4"	.083-.622	F Drill (.261-.272)	0.531	0.122	1.402	1300	890
Steel/Steel 100° Countersunk										
VC-MGL100-R8-8	M76819	MGL100-R8-8	1/4"	.169-.476	F Drill (.261-.272)	0.41	0.091	1.089	2750	2200
Aluminum/Aluminum 100° Countersunk										
VC-MGL100-B6-6	M76829	MGL100-B6-6	3/16"	.126-.331	#11 Drill (.191-.201)	0.35	0.083	0.0795	700	500
VC-MGL100-B6-9	M76830	MGL100-B6-9	3/16"	.303-.500	#11 Drill (.191-.201)	0.35	0.083	1.04	700	500
Stainless/Stainless Buttonhead										
VC-MGLP-U6-4	M76833	MGLP-U6-4	3/16"	0.62-.272	#11 Drill (.191-.201)	0.401	0.098	0.716	1349	1079
VC-MGLP-U6-7	M76834	MGLP-U6-7	3/16"	.214-.437	#11 Drill (.191-.201)	0.402	0.098	0.965	1349	1079
VC-MGLP-U6-E	M76835	MGLP-U6-E	3/16"	.062-.437	#11 Drill (.191-.201)	0.402	0.098	0.965	1349	1079
VC-MGLP-U8-6	M76836	MGLP-U8-6	1/4"	.083-.374	F Drill (.261-.272)	0.531	0.122	0.996	2360	1800
VC-MGLP-U8-10	M76837	MGLP-U8-10	1/4"	.350-.625	F Drill (.261-.272)	0.531	0.122	1.44	2360	1800
VC-MGLP-U8-E	M76897	MGLP-U8-E	1/4"	.083-.622	F Drill (.261-.272)	0.531	0.122	1.402	2360	1800

Disclaimer: The information contained in this publication is only for general guidance and is not intended to create any warranty, express, implied, or statutory. It is recommended that the user secure specific, up-to-date data and information regarding each application and/or use of such products.